

Project Name

Location

Prepared By



## SATCO S9869

3.5CFF/LED/FR/27K/120V

Notes

### General

Status	Active
Watts	3.5
Incandescent Equivalent	40
Volts	120V
Shape	CA11
Base	Candelabra
ANSI Base	E12
Finish	Frosted
CCT (Kelvin)	2700
Temperature	Warm White
CRI	80
Lumens	350
Beam Spread	360
Dimmable	Yes Dimmable
Hours Rated	15000
Lamp Type	Candle
Technology	LED

### Electrical

Operating Frequency	60 Hz
Operating Temperature	-20C (-4F) to a maximum of +45C (+113F)

### Physical

MOL	5
MOD	1.38

### Additional Information

Enclosure Rating	Enclosed Rated Lamp
Warranty	3 Year Limited

### Compliance

Safety Listing	cULus
Location Rating	Damp
Energy Star	No
CEC Status	Non-Compliant
CEC Compliant Substitute	S9618
RoHS Compliant	Yes
SDS Sheet	LED_Lamp