


Square LED Surface Mount Down Light



DIMMABLE

12", 22 watts Square LED Surface Mount Down Light is a low-profile down light intended for ceiling mount applications.



Includes

- (1) Surface mount fixture
- (1) Mounting plate
- (3) Wire Nuts
- (1) Fitting instruction
- (2) Wood screws
- *Specifications and dimensions subject to change without notice.

Features

- Driver on Board Technology, provides a 120V alternating current source and eliminates the need for traditional LED driver
- · Quick & easy to install on standard junction box, ceiling mount with mounting plate
- Die-cast aluminum housing
- · Smooth and continuous dimming, dimmable with most standard dimmers
- Rated for 50,000 hours
- · No light bulbs to replace or dispose
- Instant full brightness (including in sub-zero temperatures)
- 80+ CRI
- · cETLus listed for wet locations
- 5 year limited warranty are powder coat painted and available in the following finishes: White Gloss Enamel (WH), Bronze (BZ), Brushed Nickel (BN) and Black (BK)

| - | | | | | |
|---|---|---|--|--|--|
| _ | Specifications | | | | |
| | Electrical | Input: AC 100 – 120V 22W | | | |
| | Power Factor | 0.95 | | | |
| | LEDs | Epistar | | | |
| | LED Life | 50,000 hours | | | |
| | Lumen Output WW = Warm White NW = Neutral White | 1800 WW, 1850 NW | | | |
| | Lumen Efficacy (LPW) WW = Warm White NW = Neutral White | 82 WW, 84 NW | | | |
| | Color Temperature | Warm White 3000K Neutral White 4000K | | | |
| | CRI | ≥80 | | | |
| | Appearance Size (L x W x H) | 12" x 12" x 1" (305mm x 305mm x 25mm) | | | |
| _ | Approvals | cETLus listed for wet locations, Energy Star rated | | | |

Ordering Code

LED Color Trim Finish LVLDL - SS - 12 -WW = Warm White WH = White (3000K) BK = Black NW = Neutral White BZ = Bronze BN = Brushed Nickel (4000K)

| Project | Туре | |
|---------|---------|--|
| Date | Contact | |
| Notes | | |









