

## WB1877WOW/AF: 1 - Light Wall Sconce



### Dimensions:

<b>Width:</b>	8 5/8"	<b>Extends:</b>	4 5/8"
<b>Height:</b>	14 1/8"	<b>Wire:</b>	8"
<b>Weight:</b>	3.4 lbs.	<b>Mounting Proc.:</b>	Wall / Bath
		<b>Connection:</b>	Mounted To Box

### Bulbs:

1 - Candelabra B10 Torpedo 60w Max. 120v - Not included

### Features:

•

### Material List:

1 Body - Steel - Antique Forged Iron  
1 Cage - Steel - Weathered Oak Wood

### Safety Listing:

Safety Listed for Damp Locations

### Instruction Sheets:

**Collection:** Gannet

The Gannet lighting Collection by Feiss exudes rustic charm with a carefully crafted two-toned finish of painted, distressed Weathered Oak on an Antique Forged Iron metal frame. Clean, crisp edges and bold lines give a tailored look to this classic lantern silhouette. Gannet features open, airy frames on the sides and crown. The transitional lanterns of the Gannet Collection are offered in a 36"H x 25.5"W 6-light foyer chandelier, a 26.75"H x 18"W 4-light chandelier, a 17"H x 12"W 4-light chandelier, a dramatic 14"H x 50"L x 14"W 5-light linear island chandelier and a 12.5"H x 8.5"W 2-light wall sconce.

**UPC #:** 014817574135

**Finish:** Weathered Oak Wood / Antique Forged Iron (WOW/AF)

### Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Back Plate	11 1/4	8 5/8	5/8		7 1/8	

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	WB1877WOW/AF	1	014817574135	14	11.25	6	0.547	4.7	100	Yes
NJ Pallet		126		48	40	72	80	592.2		No
NV Pallet		126		48	40	72	80	592.2		No