

High Speed HDMI 2.0

Digital Audio & Video



DESCRIPTION

HDMI 2.0, Type-A Gold Plated, with Ethernet.
2K/4K - 2160P, 60Hz Refresh Rate.

FEATURES

- High speed HDMI Cable
- Gold Plated Contacts, Type-A 19pin
- 18Gbps - UHD 2160P
- 2K/4K - 60Hz Refresh Rate
- UL Listed RoHS Compliant
- HDCP Compliant
- CL3 Rated for In-wall installations



SKU: 242-042/50FT

Technical Data

Connector Pins	19 Pin Male, Gold Plated (Solder Type) Gold Plated
----------------	---

Jacket Construction


Material	PVC
AWG	24
Diameter	9.30±0.15mm
Color	Black
Length	50ft
RoHS Compliant	Yes

Electrical Test

1. 100% Test (open short, miss wire)
2. Contact Resistance: 3 Ohm/M
3. Insulation Resistance: DC300V 10M Ohm
4. Dielectric Strength: DC-500V/min

Marking on Jacket

High Speed HDMI® Cable with Ethernet E358133 (UL) TYPE CL3
24AWG-----AWM 20276 80°C 30V VW-1



VERTICAL CABLE

951.696.7772 California
800.749.2447 Florida
845.391.8318 New York



www.verticalcable.com

Rev. 10/2017

Specs subject to change without notice.
It is the sole responsibility of the user to have the most current specs.