



SURECRIMP® ALNS ALUM 1 HOLE LONG BARREL



- Manufactured from high strength aluminum alloy which offers maximum conductivity and excellent crimping characteristics.
- Electro-Tin plated for low contact resistance.
- Chamfered entry for easy conductor insertion.
- Color coded end cap identifies the proper compression die.
- Roll marked barrel for easy identification and proper location of crimps.
- Pre-filled with DE-OX prevents oxide from forming.
- Dual rated for Aluminum or Copper conductors.
- UL 486A/B 90° C Listed and CSA Certified.
- If proper high voltage spacing and insulation techniques are used, may be used for high voltage applications up to 35KV.
- Expanded wire size applicable when installed with specified dieless tools.
- UL File E6207

Item ID	Conductor Size	Expanded Conductor	Bolt/Stud Size	Mounting Hole	Tang Length	Tang Width	Barrel Length	Strip Length	Overall Length	Color Code	Die Index Number	Die Catalog	Outside Diameter	Inside Diameter	Standard Package	NAED/UP C Number
ALNS-500-12	500 kcmil	500 kcmil-4/0	1/2	0.5620	1.3030	1.8020	2.5650	2.6275	4.7450	PINK	300	ILD-300	1.3150	0.8540	3	0783669687736