

19221

12 X 1-1/4 PHSMS SLOT/PHIL ZIN

UPC: 085937192219

Country of Origin:

UNSPSC: 31161506

TAIWAN

Commodity: Sheet metal screws



*12 x 1-1/4" Sheet Metal Screws, Pan Head, Combo
Phillips/Slotted, Zinc*

Product Attributes

Brand Name	Minerallac Company
Sub Brand	Cully
Type	Sheet Metal Screw
Application	For use with sheet metal.
Material	Steel
Size	12 x 1-1/4" IN
Length	1-1/4" IN
Thread Type	Type-A
Thread Size	11 TPI
Head Width	0.425" IN
Head Height	0.151" IN
Head Type	Pan Head
Head Color	Silver
Finish	Zinc Plated
Drive Type	Phillips/Slotted Combo
Driver Size	#3

Compliance Information

- ☐ ARRA Compliant
- ☐ BAA Compliant
- ☐ RoHS Compliant
- ☐ UL Compliant

Item Status: Active

Standard Qty: 50

Minerallac Company

Tel: 800-927-3293

Fax: 800-824-8942

www.minerallac.com

WARRANTY DISCLAIMER The information, data and recommendations contained herein may not be all inclusive or specific to your situation, and should only be used as a guide. The information is furnished upon the condition that the person receiving it shall make his/her own determination of the suitability of the product for his/her particular use and on condition that they assume the risk of the use thereof.

With respect to this publication and the product related thereto, except otherwise expressly provided by Manufacturer in writing, MANUFACTURER MAKES NO EXPRESS OR IMPLIED WARRANTY OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE OR ANY OTHER EXPRESS OR IMPLIED WARRANTY.

Remedy/Liability Limits The exclusive remedy for losses or damages resulting from this publication or the related product (including claims based on contract, negligence, strict liability or other legal theories) shall be limited to, at Manufacturer's sole election, one of the following: 1. Refund of purchase price paid by buyer or user for product bought, or 2. Replacement of amount of product used.

Manufacturer shall not be liable for losses or damages resulting from use of this publication or handling or use of this product, IN NO CASE SHALL

MANUFACTURER BE LIABLE FOR CONSEQUENTIAL OR INCIDENTAL DAMAGES OR LOSSES, INCLUDING WITHOUT LIMIT, HEALTH RELATED DAMAGES OR INJURIES, OR LOST PROFITS.

The terms of this Warranty Disclaimer and Remedy/Liability Limits cannot be varied by any written or verbal statements or agreements. No employee or sales agent of

Manufacturer or the seller is authorized to vary or exceed the terms of this Warranty Disclaimer or Limitation of Remedies in any manner