

LED T8

L2T8/40C/10/U/G4

10 Watt LED Retrofit T8

- *Extremely long life and energy efficient*
- *No mercury*
- *Easy and safe replacement for 2 foot T8 systems*

Item #	L2T8/40C/10/U/G4-75
Product Code	79765
UPC Code	751338062665
Watts	10
Volts	100-277
Lamp Shape	T8
Base	G13 Med Bi-Pin
CRI	82
Color Temp	4000K
Initial Lumens	1,059
Beam Angle	130°
Average Rated Life	50,000
Temperature Range	-20C to 45C
MOL	24"
Replacement Wattage	17WT8
Warranty	5 years

Furnished with non-shunted lamp holder for direct connection to 120-277V supply. Ballast must be disconnected.

Specifications are subject to change without prior notice.

