



Actual



Representative

Catalog Number: 142-TB
Product ID: 7TBD012050R0004
UPC Number: 78621000142
EAN Number: 05414363101543
Status: Active

3/4 Inch Steel Locknut for Use With Rigid/IMC Conduit

- Tightens without deformation
- To effectively bond conduit or connector to box or enclosure.

Header

3D Model Available on Website

North American Specifications (UNSPSC)

UNSPSC	31161716 Locknuts
IGCC	2849 Locknuts
Brand Name	T&B
Type	Locknuts
Special Features	Hardened Steel, Malleable Iron, Copper-Free Aluminum Construction
Application	To Connect Externally Threaded Conduit or Connector to a Threadless Opening In a Box or Enclosure.
Standard	UL E23018, CSA
Material of Construction	Steel
Thread Size	3/4 Inch

European Specifications (ETIM)

ETIM	EC002382 Locknut
Material	Steel
Surface protection	Untreated
With nylon ring	N

Packaging

Inner Quantity	100
Inner Dimensions (inches)	5x4.5x3
Outer Quantity	1000
Outer Dimensions (inches)	23.75x10.75x3.75
Weight Uom	2.19 lbs. per 100

Documents / Support Tools

Technical Data Sheet US	Available on Website
Technical Data Sheet CA	Available on Website

For further technical assistance, please contact us...

Thomas & Betts - USA
 8155 T&B Blvd.
 Memphis, TN 38125
 www.tnb.com

T&B Technical Support
 MS 3B-50
 8155 T&B Blvd.
 Memphis, TN 38125

Hours: 7AM - 6PM CDT
 Monday-Friday
 Phone: (888) 862-3289
 Fax: (901) 252-1321
 Email: techsupport@tnb.com