

Catalog Number: AL250 NTN / SA4/0NTN
Product ID: 7TAA262020R0090
UPC Number: 78378669343
Status: Active



Representative

Aluminum Compression Lug, 250 kcmil, Dual Rated Aluminum or Copper 90 Degree C., Bolt 1/2 inch, Two hole NEMA pad, Length 6 inches, Barrel 1.936 inches, Pad 1.237 inch wide x 3.344 inch long x .297 inch thick. Tin Plated

North American Specifications (UNSPSC)

UNSPSC	39121448 Wire or cable compression connector
IGCC	4668 Wire or cable compression connector
Brand Name	Blackburn
Type	Compression Lug
Special Features	Dual Rated for use with Aluminum and Copper Conductors. Prefilled with Oxide Inhibitor. Marked with Conductor Sizes and Die Reference. Meet or Exceed ANSI C119.4 Specifications.
Application	General Purpose Lugs for Aluminum and Copper Terminations
Standard	ANSI C119.4
Size	Length 6 inches, Barrel 1.936 inches, Pad 1.237 inch wide x 3.344 inch long x .297 inch thick
Conductor Range	250 kcmil
Material	Aluminum
Finish	Tin Plated
Insulation	No
Temperature Rating	90 Degrees Celsius
Bolt Size	1/2 inch

Packaging

Outer Quantity	25
Outer Dimensions (inches)	7.5x6.25x7
Weight Uom	21.5 lbs. per 100

Documents / Support Tools

SDS US 1	sds-00041-tb2
----------	---------------

For further technical assistance, please contact us...

Thomas & Betts - USA
8155 T&B Blvd.
Memphis, TN 38125
www.tnb.com

T&B Technical Support
MS 3B-50
8155 T&B Blvd.
Memphis, TN 38125

Hours: 7AM - 6PM CDT
Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email:techsupport@tnb.com