



LED110WAL40KMOG-G7



Description	LED HID AREA Light Replacement 110W 14,300LM 4000K 80CRI EX39 univ burn 120-277V
Ordering Code	09647
UNSPSC Code	39101628

Specifications

Voltage Rating	100~277
Voltage Type	AC
Watts	110
Amps	1.222
Lumens per Watt	125
Base Type	Mogul Screw with Long Prong (EX39)
MOL in/mm	11.14/283
MOD in/mm	4.37/111
Lumens	14300
CT deg K	4000
CRI	80
Burning Position	Universal
Ambient Operating Temp Range	-40° C (-40° F) to 60° C (140° F)
Approvals	cULus, DLC

[watch](#) > [like](#) > [follow](#)



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 • (P) 1.800.852.2217 (F) 1.800.492.8975
Canada: 81 King St, Barrie, ON L4N 6B5 • (P) 1.888.410.8151 (F) 1.888.705.1335