



8736301EN3-71: Large One Light Outdoor Wall Lantern Dimensions:



Width: 9"

Height: 21 1/4"

Weight: 6.2 lbs.

Extends: 11 3/4"

Wire: 6" (color/Black/White)

Mounting Proc.: Cap Nuts

Connection: Mounted To Box

Bulbs:

1 - LED Medium A19 9.5w Max. 120v - included

Features:

- ENERGY STAR® Qualified
- LED Bulbs are an efficient, versatile and durable light source that deliver exceptional performance.
- Meets Title 24 energy efficiency standards
- Title 24 compliant when used with included Joint Appendix (JA8) approved lamp.

Material List:

1 Body - Die Cast Aluminum - Undefined
1 Cap - Die Cast Aluminum - Undefined
1 Canopy - Die Cast Aluminum - Undefined

Safety Listing:

Safety Listed for Wet Locations

Instruction Sheets:

Trilingual (English, Spanish, and French) (990W8_36301-CHI)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Panel	Glass	Satin Etched	4	G560223-619								
Panel	Glass	Satin Etched	4	G560224-619								

Backplate / Canopy Details:

Type	Height / Length	Width	Depth	Diameter	Outlet Box Up	Outlet Box Down
Back Plate	9 3/8	4 7/8	7/8		10 1/4	11

Replacement Bulb Data:

Product #			Type	Base	Watts	Watts Consumed	Volts	Hours	Lumens	Temp (°K)	CRI
97502S	Frosted		A19	Medium	9.5	9.5	120v	15000	800 230°	3000	90

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	8736301EN3-71	1	785652044960	22.75	11.75	14.25	2.204	8.1	250	Yes
NJ Pallet		36		48	40	74	82.222	291.6		No
NV Pallet		36		48	40	74	82.222	291.6		No