



Representative

**Catalog Number:** 5265  
**Product ID:** 7TAD012070R0003  
**UPC Number:** 78621005265  
**EAN Number:** 05414363075547  
**Status:** Active

Liquidtight Sealing Gasket, 1-1/4 Inch, with 316 Stainless Steel Retainer and Santoprene Sealing Material

- Design locks resilient sealing material in stainless steel.
- Stainless steel retainer protects seal from extruding out under torque and limits compression to an optimum predetermined value; provides high quality seal.
- Resilient material flows and seals rough edges.

#### Header

3D Model Available on Website

#### North American Specifications (UNSPSC)

UNSPSC	39121420 Liquid tight connectors
IGCC	4585 Liquid tight connectors
Brand Name	T&B
Type	Sealing Gaskets
Application	When used with an externally threaded connector provides a tight seal against oil, fumes or moisture at the knockout opening.
Standard	UL E13938, CSA
Size	1-1/4 Inch
Material	Stainless Steel

#### European Specifications (ETIM)

ETIM	EC001181 Sealing ring
Model	O-ring
Material	Other
Fitting for thread size NPT	1.25

#### Packaging

Inner Quantity	5
Inner Dimensions (inches)	3.3x2.8x2.3
Outer Quantity	25
Outer Dimensions (inches)	9.5x6.06x3.38
Weight Uom	2.5 lbs. per 100

#### Documents / Support Tools

Technical Data Sheet CA	Available on Website
Technical Data Sheet Global	wsd-001558

For further technical assistance, please contact us...

Thomas & Betts - USA  
 8155 T&B Blvd.  
 Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
 MS 3B-50  
 8155 T&B Blvd.  
 Memphis, TN 38125

Hours: 7AM - 6PM CDT  
 Monday-Friday  
 Phone: (888) 862-3289  
 Fax: (901) 252-1321  
 Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)