

4/8 CKT 125A SURF 125A 1PH MLO 4/8C 12 IN. BOX INDOOR  
LDCNTR MURRAY



### General technical data

Configuration of the busbars	125A
Mounting type	Surface
Phase number	1
Suitability for operation	Residential

### Electricity

Ampacity	125 A
Voltage between phase and Ground (GND) rated value	120 V
Voltage between phase and phase rated value	240 V

### Switching capacity

Switching capacity current acc. to EN 60898 rated value	22000 A
---	---------

### Model

product brandname	Murray
Product sub brand name	Load Centers

### Mechanical Design

Number of width units for installation width	4
--	---

Size of the circuit-breaker	ML
Width [in]	1865.325 in
<b>last modified:</b>	02/22/2017