



Actual



Representative

Catalog Number: 3302M-TB
Product ID: 7TAA106090R0001
UPC Number: 78621080552
EAN Number: 05414363141051
Status: Active

Sheathed Cable Fitting, Straight, Knockout Size 1/2 Inch, Nylon Insulated, Two Screw Connector, Steel with Zinc Plating

North American Specifications (UNSPSC)

UNSPSC	39121419 Flex connectors
IGCC	4573 Flex connectors
Brand Name	T&B
Sub Brand	UL E17583, CSA
Type	Non-Metallic Sheathed Cable Conduit Fittings
Special Features	Rounded Cable Grip and Smooth Bushing Protect The Cable Sheath and Wire Insulation. Since Saddle is Threaded, Screws Do Not Travel or Extend Beyond The Connector Body As It is Clamped to The Cable. An Extra Lip on The Saddle Closes The Unused Part of The Connector Opening.
Application	To Connect Non-Metallic Sheathed Cable and Flexible Cord to a Box or an Enclosure.
Standard	UL E23013, CSA 2884
Size	1/2 Inch
Material	Steel
Finish	Electro Zinc Plated
Color	Metallic
Insulation	Nylon

European Specifications (ETIM)

ETIM	EC001180 Screw connection for protective metallic hose
Nominal size in inch	1/2 inch
Model	Straight
Revolving thread	N
Construction type	External thread
Connection type screw connection to housing	Other
Material housing	Steel
Surface protection	Zinc coated

Packaging

Inner Quantity	100
Inner Dimensions (inches)	9.6x6.7x4.7
Outer Quantity	500
Outer Dimensions (inches)	23.5x7.2x10.4
Weight Uom	5 lbs. per 100

Documents / Support Tools

Technical Drawing / Data Sheet US	Available on Website
-----------------------------------	----------------------

Header

3D Model	Available on Website
----------	----------------------

For further technical assistance, please contact us...

860 Ridge Lake Blvd.
Memphis, TN 38120
www.tnb.com

MS 3B-50
860 Ridge Lake Blvd.
Memphis, TN 38120

Monday-Friday
Phone: (888) 862-3289
Fax: (901) 252-1321
Email: techsupport@tnb.com