


## SPECIFICATION SHEET: NPY-120-226-CFL


This Is An Original Product From Fulham Co., Inc

Description: PONY Series, High Frequency Electronic, Rapid Start Ballast,

\* Meets Energy Star 4.0 Criteria For Applications Listed.

This Ballast Will Operate Following Lamps.









## **ELECTRICAL DATA**

INPUT VOLT: 120V ± 10%, 50/60Hz										
LAMP WATTS/TYPE	18CFT/E	*24/27CFT/E	*26CFQ/E	26CFTR/E	22CRT9	-	-		-	-
LAMPS OPERATED	2	2	2	2	2					
INPUT WATTS	38.75	51.13	58.06	55	43.44					
LINE CURRENT:	0.566	0.730	0.805	0.780	0.633					
POWER FACTOR	0.569	0.582	0.597	0.590	0.572					
BALLAST FACTOR	1.014	0.991	1.058	1.004	1.028					
EFFICACY FACTOR	2.616	1.939	1.822	1.826	2.366					
THD	142.17	135.87	130.07	131.00	141.17					
CURRENT CREST FACTOR	< 1.7									
EMI/RFI COMPLIANCE	FCC PART 18-B (Consumer)									
SOUND RATING	" A "									
BALLAST TYPE	RAPID START									
VOLTAGE TRANSIENTS	ANSI 62.41									
INPUT/PROTECTION	FUSE									
OUTPUT/PROTECTION	EOL									
MIN. OPERATING TEMP	0 °C ( 32 ° F )									
MAX. CASE TEMP	75 °C ( 167 ° F )									
ENERGY STAR 4.0	YES									
APPROVALS/CLASS	UL /cUL LISTED, CLASS " P ", 1 OUTDOOR									





Fulham extends a limited warranty only to the original purchaser or to the first user for a period of <u>2 years</u> from the date of manufacture when properly installed and operated under normal conditions of use. For complete terms and conditions, please reference the Fulham product catalog (www.fulham.com)

Due to a program of continuous improvement, Fulham reserves the right to make modifications or variations in design or construction to the equipment described.

2006-10 rev E