

6" Regressed Gimbal LED 15W Warm White

Type IC, Wet & Air-Tight



Project:		
Location:		
Trim Finish:	Qty:	
Notes:		

DESCRIPTION

1 1/2" Regressed 6" Gimbal Round LED With Integral Driver In Connection Box. Fits Where No Other Recessed Fixture Can.

Unique Design: Gimbal Yet Air-Tight Without Housing Needed.

FEATURES & BENEFITS

3 1/2" Thin - Install Where Ceiling Space Is Limited.

Type IC Rated - No Housing Required
Fast & Easy To Install - Save On Labour

Driver Inside Connection Box - No Junction Box Needed


Directional Beam - Great for Sloped Ceilings and Highlighting Artwork


CRI 90+ for True Colour Rendering

MOUNTING

Cut Hole In Ceiling And Snap Fixture In Opening With Attached Spring Clips. Ceiling Clearance Required: 3 1/2"

<u>DIMENSIONS</u> ID 5 1/4" OD 7 1/2" Cut Out 5 1/4" to 6"





<u>Driver Included</u>

Cable Rating FT4 / CM



Available Trims





e Black







Canadian Patent No. 2,967,954 and United States Patent Pending





Warehouses

Vancouver Toronto Las Vegas Naples Philadelphia Dallas Seattle Chicago Denver

tel: 1-844-24-LOTUS (56887)

fax. 1-877-561-6306

www.lotusLEDlights.com

CHARACTERISTICS

Unique Design: 1 1/2" Regressed 6" Gimbal with 20° tilt and 360° rotation,

Yet Air-Tight Without Housing Needed. Patent Pending.

Body: Durable, Die Cast Aluminum Alloy for Optimal Heat Dissipation.

Paint: Oil Based Spray Painted - Scratch Resistant And Smooth Finish.

LED: Epistar COB Custom Packaged by Hongli Tronic with LM80.

Guaranteed 98% Lumen Maintenance After 6,000 Hours.

Strict Binning To Ensure Consistent Light Colour. CRI 92 for True Colour Rendering.

Driver: 4th Generation Lotus Designed. Field Proven Since 2011.

Connection Box: Patented Invention By Lotus LED Lights.

Saves Contractors Labour On Installation.

Testing: Every Single Driver Is Powered For Minimum 24 Hours Together With The

Fixture That It Is Shipped With. No Random Tests - We Hand Test Every Fixture & Driver.


PHOTOMETRIC DATA OF A LAB TESTED SAMPLE

 MODEL:
 LRG6-27K
 LAMP FLUX:
 1210 LM


 VOLTAGE:
 120 V
 LUMENS / POWER:
 84 LM/W

 POWER:
 14.44
 CENTRAL INTENSITY:
 1992 CD

 PF:
 0.99
 BEAM ANGLE:
 42 DEGREES



Max , Ave Beam angle of C0plane43.82



ORDERING GUIDE

Example: LRG6 - 27K - WH

LRG6 - 27K -

Trim Finish

WH: White

BK : Black

Order 277V - 347V Optional Driver Separately As cat # LLL-LD1535H



ACCESSORIES



Low Volage Extension Cables 6ft - cat # EXC6, 20ft - cat # EXC20 Max 40 ft Extension Allowed

LOTUS LED Lights

1200

80

90

2700 (Warm White)

lighting facts

All results are according to IESNA LM-79-2008: Approved Method for the Electrical and

Visit www.lightingfacts.com for the Label Reference Guide

Light Output (Lumens)

Color Accuracy

Lumens per Watt (Efficacy)

Registration Number: K53C-WA6E4J (10/26/2017) Model Number: LRG6-27K Type: Luminaire - Downlight

Watts



Flat Rough-In Plate - cat # RIP6



Flanged Rough-In Plate - cat # LRP6



Warehouses

Vancouver Toronto Las Vegas Naples Philadelphia Dallas Seattle Chicago Denver tel: 1-844-24-LOTUS (56887) fax. 1-877-561-6306 www.lotusLEDlights.com