# C-CP-A-SQ-79L Series

LED Square Canopy Light Replaces 150W PSMH/175W MH



# EXTREMELY DURABLE DESIGN AND AN EFFICACY UP TO 110 LUMENS PER WATT.



### PRODUCT SPECIFICATIONS

#### **OVERVIEW**

• Initial Delivered Lumens: 7,900

• CRI: ≥ 70

• CCT: Neutral White 4000K, Cool White 5000K

• Input Power: 74 Watts

• Dimmable: No

• Operating Minumum: -40°C (-40°F)

• Lifespan: Estimated >100,000 Hours

• Power Factor: > 0.9

Total Harmonic Distortion: < 20%</li>

· Limited Warranty: 5 Years\*

Replaces 150W PSMH/175W MH

PERFORMANCE	DURABLE	RECOMMENDED USE	INPUT VOLTAGE
<ul> <li>Uses 66% less energy than comparable HID fixtures</li> <li>Delivers up to 15% more light than comparable HID fixtures</li> <li>Type VS distribution pattern</li> </ul>	<ul> <li>Polyester powder-coat finish for long-lasting color</li> <li>UV-stabilized lens designed to last</li> </ul>	<ul><li> Security</li><li> Entryways</li><li> Perimeter Lighting</li><li> Exterior Canopies</li></ul>	• Universal (120V through 277V Operation)

# **ORDERING INFORMATION**

Example: C-CP-A-SQ-79L-40K-WH

C-CP-A	SQ	79L		
PRODUCT	STYLE	LUMEN PACKAGE	CCT	COLOR
C-CP-A	<b>SQ</b> LED Square Canopy	<b>79L</b> 7,900 Lumens 74W	40K Neutral White (4000K) 50K Cool White (5000K)	<b>DB</b> Dark Bronze <b>WH</b> White


### **CERTIFICATIONS:**







# C-CP-A-SQ-79L Series



### **SERIES OVERVIEW**

DIMENSIONS	PRODUCT WEIGHT	MOUNTING HEIGHT	SPACING
10-7/8" L x 10-7/8" W x 5-1/2" H 13-1/3" L x 13-1/3" W (Outer Edge)	8.54 lbs.	10 to 20 feet	2 to 3 times the mounting height

# **FIXTURE SPECIFICATIONS**

HOUSING	Low-copper, die-cast aluminum housing Dark bronze or white polyester powder-coat finish
LENS ASSEMBLY	UV-stabilized acrylic prismatic refractor with self-retaining screws
MOUNTING	3/4" conduit entry on top for pendant mounting 1/2" conduit entries on two sides

# **ELECTRICAL PERFORMANCE**

OPERATING MINUMUM	LIFESPAN L <sub>70</sub> at 25°C (77°F)	POWER FACTOR	TOTAL HARMONIC Distortion	DIMMABLE
-40°C (-40°F)	Estimated >100,000 Hours	> 0.9	< 20%	No
INPUT VOLTAGE	120V	208V	240V	277V
CURRENT DRAW (Amps)	0.62A	0.36A	0.31A	0.27A

# **WARRANTY AND CERTIFICATIONS**

WARRANTY	UL LISTED	DLC
5 Year Limited*	Wet Locations	DLC Qualified



CA RESIDENTS WARNING: Cancer and Reproductive Harm – www.p65warnings.ca.gov

© 2018 Cree, Inc. and/or one of its subsidiaries. All rights reserved. For informational purposes only. Content is subject to change. Patent www.cree.com/patents. C-LITE™ and the C-LITE logo are trademarks of Cree, Inc. The UL logo is a registered trademark of UL LLC. The DLC QPL logo is a registered trademark of Efficiency Forward, Inc

**US: c-lite.com** T (800) 236-6800 F (262) 504-5415

**Canada: www.cree.com/canada** T (800) 473-1234 F (800) 890-7507

