



Actual

**Catalog Number:** 4170-C  
**Product ID:** 7TAA040420R0016  
**UPC Number:** 78635850915  
**Status:** Active

Round Ceiling/Fixture Nail-On Bracket Outlet Box, Volume 21.5 Inches, Diameter 4 Inches, Depth 2-7/16 Inches, Color Brown, Material Phenolic, Mounting Means Compound Angled Side Nails, with High Clamps

**North American Specifications (UNSPSC)**

UNSPSC	39121316 Ceiling box
IGCC	4448 Ceiling box
Brand Name	Carlon
Type	Ceiling Boxes
Special Features	High clamps
Application	Suitable for fixture support up to 50 lbs.
Standard	UL e11461
Material	Phenolic
Color	Brown
Mounting	Angled nails and #3 bracket
Cubic Capacity	21.5
Knockouts	No

**European Specifications (ETIM)**

ETIM	EC002601 Box/housing for built-in mounting in the wall/ceiling
Mounting method	Other
Shape	Round
Construction type	Device connection box (round/square)
Equipped with	Mounting plate
Diameter	101.6mm
Depth	-mm
Mounting switching equipment	Screwing
Pipe locking	N
Pipe locking optional	N
Surface protection	Other
Cover	None
Cover attachment	Not applicable

**Packaging**

Outer Quantity	50
Outer Dimensions (inches)	20.25x16.5x8.75
Weight Uom	47.69 lbs. per 100

**Documents / Support Tools**

Technical Data Sheet US	Available on Website
-------------------------	----------------------

**For further technical assistance, please contact us...**

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
www.tnb.com

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email:techsupport@tnb.com