



GE
Lighting

18275 - GE rough service work light 100 watt A21 1-pack

100A/RS 12PK-5

- ☞ GE's specialty bulbs offer innovative solutions for a variety of lighting needs.
- ☞ The GE Rough Service Worklight is specially designed with rugged filaments and mounts to withstand rough handling and shock better than regular household bulbs.
- ☞ 120 volts
- ☞ Estimated yearly energy costs \$12.05 based on 3 hours per day \$0.11 per kWh
- ☞ Lasts .9 years based on 3 hours per day usage
- ☞ 2800K soft white light appearance
- ☞ A21 shape with medium base for use in rough service applications
- ☞ GE rough services worklight bulbs are specially designed with rugged filaments and mounts to withstand rough handling and shock better than regular household bulbs

CAUTIONS & WARNINGS

Warning

Unexpected lamp rupture may cause injury, fire, or property damage
Avoid direct water/liquid contact.

Risk of Fire

Keep combustible materials away from lamp.

GENERAL CHARACTERISTICS

Base Description	Medium Screw
Base Type	Screw-In
Bulb Finishes and Colors	Inside frost
Filament	C-7A
Rated Life Hours-nominal	1000 h
Primary Application	Rough Service
Bulb Material	Soft glass
Product Technology	Incandescent
Base	E26
Bulb Shape	A21

PHOTOMETRIC CHARACTERISTICS

Nominal Initial Lumen per Watt	12
Initial Lumens-nominal	1230 lm

PRODUCT INFORMATION

Product Code	18275
Description	100A/RS 12PK-5
Alternative Unit Of Measure	EACH
Standard Package Quantity	60
Ean UPC	043168904124
Standard Package GTIN	00043168904124
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	60
Sales Unit	Each
UCC	043168182751
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168904124
Standard Package GTIN	00043168182751
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168182751

DIMENSIONS

Diameter	2.62 in
----------	---------

ELECTRICAL CHARACTERISTICS

Wattage	100 W
Input Voltage [nom]	120 V