



GE
Lighting

21734 - GE R40 - Reflector Flood

500R/3FL

GENERAL CHARACTERISTICS

Base Description	Mogul Screw
Base Material	Brass
Base Type	Screw-In
Bulb Finishes and Colors	Frost
Filament	CC-2V
Rated Life Hours-nominal	2000 h
Primary Application	Reflector Flood
Bulb Material	Heat resistant glass
Product Technology	Incandescent
Base	E39
Bulb Shape	R40

PHOTOMETRIC CHARACTERISTICS

Center Beam Candle Pwr Candela	8000 cd
Nominal Initial Lumen per Watt	12
Initial Lumens-nominal	6000 lm

PRODUCT INFORMATION

Product Code	21734
Description	500R/3FL
Alternative Unit Of Measure	CASE
Standard Package Quantity	
Ean UPC	043168217347
Standard Package GTIN	10043168217344
No Of Items Per Sales Unit	
No Of Items Per Standard Package	
Sales Unit	Case
UCC	043168217347
Alternative Unit Of Measure	EACH
Standard Package Quantity	24
Ean UPC	043168217347
Standard Package GTIN	00043168217347
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	24
Sales Unit	Each
UCC	043168217347

DIMENSIONS

Diameter	5.0 in
----------	--------

ELECTRICAL CHARACTERISTICS

Wattage	500 W
Input Voltage [nom]	120 V

CAUTIONS & WARNINGS

Warning

Unexpected lamp rupture may cause injury, fire, or property damage
Avoid direct water/liquid contact.

Risk of Fire

Keep combustible materials away from lamp.
Use in fixture rated for this product.

NOTES

Collector grid.