

APPLICATIONS

This strip light is mainly for commercial use. It can be used in warehouse, office, garage, displays, shops and other commercial applications.

FEATURES & BENEFITS

- Min CRI 80
- Input voltage can be AC100-277V
- Reduces energy consumption up to 60%
- 5 year warranty
- Surface/pendant mounting installation
- Suitable for damp locations
- Glass free design

SIZE:

4 ft - 42.44"L x 3.75"H x 3.25"W 8 ft - 90.46"L x 3.75"H x 3.25"W



ORDERING DATA

EXAMPLE: LSAR48LED40DMV40



LED 48 48" 96 96"

Wattage / Lumens 48 inch

40 40 Watts 5400 Lumens 96 inch **60** 60 Watts 8400 Lumens

Driver Type DMV 120-277VAC Multi-Volt 0-10V Dimmable


Color Temp 40 4000K 50 5000K



ACCESSORIES

Wire guard (4 clips included) Δ42 White wire guard (4 clips included) A42W A349 Replacement clips (QTY 4)





MOUNTING OPTIONS:

- A. Keyhole slots for surface mounting
- B. Wiring knockouts
- C. T-bar clip mounting hole
- D. V-Hook openings for chain mounting

DLC Premium	
LSAR48-LED40DMVxx	xx=30,35,40,50
LSAR96-LED60DMVxx	xx=30,35,40,50
LSAR96-LED68DMVxx	xx=30,35,40,50

Dimensions and specifications subject to change without notice.





800-444-WATT

♦ www.mobern.com ♦ 8200 Stayton Dr., Ste. 500, Jessup, MD 20794

CAT# JOB NAME

TYPE