



Description	1000W HPS ED-25 Mogul Base
Ordering Code	15324
UNSPSC Code	39101617

Specifications

Voltage Rating	250
Watts	1000
Base Type	Mogul Screw (E39)
Bulb Type	E25
MOL in/mm	15.06/382.6
MOD in/mm	3.11/79.0
LCL in/mm	8.75/222.3
Mercury Content (mg)	12.5
HG Form	liquid
Approx Initial Lumens	140000
Approx Mean Lumens	126000
CT deg K	2100
CRI	21
Rated Life	24,000
Common Code	C1000S52
ANSI Ballast	S52
Fixt Rqmt	Open
Burning Position	Universal
Coating	Clear
Approvals	IMERC, TCLP Compliant

watch > like > follow



selection. solutions. simplicity. eiko.com

23220 W. 84th St, Shawnee, KS 66227 • (P) 1.800.852.2217 (F) 1.800.492.8975
Canada: 81 King St, Barrie, ON L4N 6B5 • (P) 1.888.410.8151 (F) 1.888.705.1335