



- Replaces 26, 32, and 42 watt CFLs
- Direct Replacement - for use with Electronic, Instant Start, Rapid Start, and Programmed Start ballasts with no rewiring required. Ballast required.
- Instant on to full brightness / no flickering
- Horizontal operation
- Up to 70% energy saving
- Long life - 50,000 hours
- 5 year warranty

S29852

View:

Emergency Ballast Compatibility Chart

Item Number	UPC	Watts	Fluorescent Equivalent	Lamp Shape	Base	Lamp Code	Dimmable/Non-Dimmable	
S29852	045923298523	9	26, 32, and 42 watt CFL	PL	G24q	9WPLH/LED/840/DR/4P	Non-Dimmable	
Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours		Kelvin Temp	Color	CRI
Frost	6-5/8"	1-3/32"	1000	50000		4000	Cool White	82
Beam Spread Deg	Operating Temperature	Package Type	CEC Status	DLC ID:		RoHS Compliant	UL or ETL Listed	UL Classification
120	-20C (-4F) to a maximum of +45C (+113F)	Box	Lawful for sale in California	PLTQJ675TIRG DLC Search		Yes	Yes	cULus Classified - Damp Location Rated
Warranty								
5 Year Limited								



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027



©2012, Satco Products, Inc. Not responsible for typographical errors. 06/12 S1051