



Powering Business Worldwide

pe.eaton.com

BR style 1-inch loadcenter

BR24L70FP

UPC: 786676001847

Dimensions: 3.88 IN * 14.31 IN * 23 IN (L * W * H)

Notes: Ground bar kit priced separately. Suitable for use as service equipment when no more than 2 service disconnecting mains are provided or when not used as lighting & appliance panelboard

Warranty: 10 year

Specifications:

- **Special Features:** Current design
- **Type:** Main lug
- **Amperage Rating:** 70A
- **Box Size:** 5
- **Bus Material:** Aluminum
- **Cover:** Cover not included
- **Enclosure:** NEMA 1
- **Enclosure Material:** Metallic
- **Interrupt Rating:** 10 kAIC
- **Main Circuit Breaker:** BR
- **Mounting:** Flush
- **Number Of Circuits:** 4
- **Number Of Poles:** Four-pole
- **Number Of Spaces:** 2
- **Number Of Wires:** Three-wire
- **Phase:** Single-phase
- **Used With:** Type BR 1-inch breakers
- **Voltage Rating:** 120/240V
- **Wire Size:** #8-#2 AWG Cu/Al at 60°C or 75°C

Supporting documents:

- [Eatons Volume 1-Residential and Light Commercial](#)
- [Cutler-Hammer Type CH and BR Loadcenters - Instructions](#)
- [Type BR Arc Fault Circuit Breakers and](#)



[Loadcenters](#)

- [Eaton Specification Sheet - BR24L70FP](#)

Certifications: No Data

Product compliance: No Data

© 2016 Eaton. All rights reserved.