



Powering Business Worldwide

pe.eaton.com

Type CL 1-inch Classified Replacement Breaker

CL215

UPC:786676011624

Dimensions:

- **Height:** 3 IN
- **Length:** 3 IN
- **Width:** 2 IN

Weight:.5 LB

Notes:Replacement for Square D Homeline, GE Type THQ, Crouse-Hinds Type MP, Thomas and Betts Type TB, Murray Type MP, ITE/Siemens Type QP. Requires Two 1-inch (25.4 mm) spaces.

Warranties:

Specifications:

- **Amperage Rating:** 15A
- **Interrupt Rating:** 10 kAIC
- **Number Of Poles:** Two-pole
- **Voltage Rating:** 120/240V
- **Main Circuit Breaker:** CL
- **Trip Type:** Common
- **Wire Size:** #14-4 AWG Cu/Al 60°C or 75°C
- **Used With:** Type CH Loadcenters

Supporting documents:

- [Eatons Volume 1-Residential and Light Commercial](#)
- [Eaton Specification Sheet - CL215](#)

Certifications:

- UL 489

Product compliance: No Data

