



# S9924

43T8/LED/96-840/BP/R17d  
43 watt T8 LED; 4000K; Recessed Double Contact base; 50000  
Average rated hours; 5500 Lumens



## Features

- Direct wire 120-277V line voltage
- Double ended wiring
- No ballast or external driver required
- All glass tube
- Shatterproof coated
- NSF certified

S9924

Item Number	UPC	Voltage	Watts	Operating Frequency	Fluorescent Equivalent	Lamp Shape	Base
S9924	045923099243	120-277	43	50/60Hz	110W (T12)	T8	Recessed Double Contact HO/VHO

ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours
R17d	43T8/LED/96-840/BP/R17d	Non-Dimmable	White	96"	1.00"	5500	50000

Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature	Pack	Package Type	CEC Status
4000	Cool White	82	210	-20C (-4F) to a maximum of +45C (+113F)	10	Eggcrate	Lawful for sale in California
RoHS Compliant		UL or ETL Listed		UL Classification		Warranty	
Yes		Yes		cULus - Damp Location Rated		<a href="#">5 Year Limited</a>	



National Toll-Free:  
800.43.SATCO  
(800.437.2826)  
[www.satco.com](http://www.satco.com)

Distribution Centers:  
New York, Florida, Texas,  
Washington, California,  
Puerto Rico

Corporate Offices:  
110 Heartland Blvd.,  
Brentwood, NY 11717  
800.437.2826 631.243.2022  
Fax 631.243.2027



©2012, Satco Products, Inc. Not responsible for typographical errors. 06/12 S1051