











View More +

48-03-3135



SDS+ DUST TRAP™ Drilling Shroud (Bulk 10)

No Reviews Write the First Review (https://www.milwaukeetool.com/write-review/?pr_page_id=48-03-3135&pr_merchant_id=375152&pr_api_key=dd031606-9334-476a-906e-368515eeaad9&pr_merchant_group_id=14854)

The Milwaukee® SDS Plus DUST TRAP™ is the industry's first OSHA® compliance solution without a vacuum, ideal for overhead drilling applications. The universal fit allows the DUST TRAP™ to work with all SDS Plus rotary hammers and SDS Plus drill bits up to an 8" length, including stop bits and other anchor installations tools. The clear sleeve allows visibility while the locking mechanism enables easy storage on the jobsite. The compact, collapsible design is ideal for tough to reach places, providing superior productivity. The DUST TRAP™ is OSHA® objective data compliance solution when used without a vacuum and OSHA® Table 1 compliant when used with a dust extractor, giving users the flexibility to adjust to the daily demands of the jobsite while being compliant. Replacement SDS+DUST TRAP™ Sleeves are available (48-03-3235).

Close

INCLUDES:

(1) SDS+ DUST TRAP™ Drilling Shroud (Bulk 10) (48-03-3135) (/Products-Repository/North-America/Accessories/Drilling/Concrete-Drilling/Vacuum-Drill-Bits-and-Dust-Management/Dust-Trap/48-03-3135)

No Sellers Found

KEY FEATURES

SPECIFICATIONS

REVIEWS

OSHA Compliance without a Vacuum

Universal Fit for SDS-Plus Rotary Hammers

Clear sleeve for maximum visibility and accuracy

OSHA® Objective Data compliance without a dust extractor

OSHA® Table 1 compliant with a dust extractor

Fits SDS Plus drill bits up to 8" overall length and works with stop bits

Compact, collapsible design ideal for accessibility and storage

Download Objective Data (/-/media/PDFs/Objective-Data/Milwaukee-DUST-TRAP-Objective-Data1.ashx)

PRODUCT SPECIFICATIONS

Height	6.89"
Width	4.17"
Length	12.48"
Pack Qt	y 10

Write the First Review (https://www.milwaukeetool.com/write-review/?pr_page_id=48-03-3135&pr_merchant_id=375152&pr_api_key=dd031606-9334-476a-906e-368515eeaad9&pr_merchant_group_id=14854)

SIGN ME UP!

Be the first to know about special offers, new product launches and events.

Trade* Email Address* Zip Code* Select a Trade

Subscribe

(https://nthpw//interest/full/https://nthpw//

PRODUCTS

Power Tools (/Products/Power-Tools)

Lighting (/Products/Lighting)

Hand Tools (/Products/Hand-Tools)

Storage (/Products/Storage-Solutions)

Work Gear (/Products/Work-Gear)

Instruments (/Products/Instruments)

Accessories (/Products/Accessories)

ABOUT US

Milwaukee Story (/Company/Milwaukee-

Press Releases (/News/Press-Releases)

Milwaukee Swag

(https://www.milwaukeetoolswag.com)

Careers (https://www.milwaukeetool.jobs/)

Contact Us (/Contact)



US:: EN - Change Site / Language (/Country-Selector)



Where to Buy Milwaukee Products (/Buy-Now)

NEW PRODUCTS

M18 FUEL™ High Torque ½" Impact Wrench with Pin Detent - 2766-20 (/Products/Power-Tools/Fastening/Impact-Wrenches/2766-20)

M18 FUEL™ Drain Snake w/ CABLE DRIVE™ - 2772A-20 (/Products/Power-Tools/Drain-Cleaning/Sink-Machines/2772A-20)

M18™ RADIUS™ Site Light/Charger w/ ONE-KEY™ - 2150-20 (/Products/Lighting/Site-Lights/2150-20)

PACKOUT™ Rolling Tool Box - 48-22-8426 (/Products/Storage-Solutions/PACKOUT/PACKOUT-Tool-Boxes/48-22-8426)

SHOCKWAVE Linemans Impact Auger Bits (/Products/Accessories/Metal-Drilling/Wood-Boring-Bits/SHOCKWAVE Linemans Impact Auger Bits)

HOW CAN WE HELP?

Contact Us (/Contact)

eService Repair (/eService)

Find A Service Center (/Support/Find-A-Service-Center)

Manuals and Downloads (/Support/Manuals-and-Downloads)

Work At Milwaukee (https://www.milwaukeetool.jobs/)

© 2018 by Milwaukee Tool. All rights reserved.

Legal (/Footer/Legal) | Safety Notices (/News/Safety-Notices) | Privacy (/Footer/Privacy) | Contact Us (/Contact)