

#### Project:

Fixture Type:

Contact:

## 60" Ceiling Fan

Ceiling mounted • Dry location listed PROGRESS LED

### **Description:**

Images:

The 60 inch Glandon ceiling fan features a 17W LED module (3000K color temperature) with a shatterproof white opal shade. With a sophisticated and modern design, Glandon has a dual mount system and comes with a hand held 3-speed remote control with full range dimming is included. It comes with reversible blades in driftwood and toasted oak.

#### **Specifications:**

- · Gilded Iron (-71) (painted)
- Steel Construction
- White Opal Polycarbonate diffuser
- The 60" Glandon ceiling fan features a dimmable 17W LED module with a shatterproof white opal shade
- 3000K color temperature, 90CRI LED replaceable light module and 1400 lumens (source)
- Glandon ceiling fan features reversible Walnut/Driftwood blades with a Gilded Iron finish
- Beautiful and expansive in design, the 60" Glandon ceiling fan is ideal for use in large indoor spaces, such as great rooms, living rooms and other spacious areas
- A sophisticated and modern design, the 60" Glandon six-blade ceiling fan includes reversible blades that will complement any decor
- Glandon features a dual mount system to offer greater flexibility when installing the fan can be installed on a flat or sloped ceiling
- As a general rule of thumb, lighting experts suggest this fan is ideal in a room size that is larger than 400-square feet
- · Rated for indoor use, dry location listed
- · Reversible motor for year round comfort allows you to choose either a down draft (summer) or an up draft (winter)
- A hand held 3-speed remote control with full range dimming is included.
- Remote control may be replaced by a P2630-30 wall control
- A 3/4" x 6" downrod is included. Longer accessory downrods can be ordered separately
- Can be used to comply with California Title 20.
- Can be used to comply with California Title 24.
- High Speed Energy Information: Airflow- 6036 cfm, Energy consumption- 84 watts (excluding lights), Airflow efficiency- 81 cfm/watt
- Dimmable to 10% brightness (See Dimming Notes)
- Canopy covers a standard 4" octagonal recessed outlet box
- Mounting strap for outlet box included
- 80" of wire supplied
- Meets California Title 24 JA8-2016

#### Performance:

Input Power	17w
Input Voltage	120 V
Input Frequency	60 Hz
Lumens/LPW (Source)	1386/77 (LM-82)
ССТ	3000 K
CRI	90 CRI
Life (hours)	50,000 (L70/TM-21)
FCC	FCC Title 47, Part 15, Class B
Min. Start Temp	-10 °C
Max. Operating Temp	40 °C
Warranty	Limited Lifetime warranty
Labels	UL Dry location listed
	Meets California Title 24 JA8-2016





P2586-7130K

#### **Dimensions:**

Diameter: 60" Height: 17-1/8"

Diffuser Width: 7-1/4" Height: 0-7/8"



# 60" Ceiling Fan

Ceiling mounted • Dry location listed PROGRESS LED

### P2586-7130K

#### **Dimming Notes:**

P2586 is designed to be compatible with many Triac/Forward Phase or ELV/Reverse Phase controls.

The following is a partial list of known compatible dimmer controls.

#### **Dimming Controls**

Lutron - NTEVL-300		
Lutron - DVELV-300P		
Lutron - Caseta Wireless		
Leviton – 6672		
Leviton — 6674		
Lutron - AYCL-153P		
Lutron - AYLV-600P		
Lutron - MAELV-601		
Leviton - AWRMG-FAW		

Dimming capabilities will vary depending on the dimmer control, load, and circuit installation. Always refer to dimmer manufacturer instructions or a controls specialist for specific requirements.

Dimmer control brand names where identified above are trade names or registered trademarks of each respective company.