



### M12™ REDLITHIUM™ XC 4.0 EXTENDED CAPACITY BATTERY

Delivers up to 2X more runtime, 20% more power and 2X more recharges than standard lithium-ion batteries. •REDLINK™ Intelligence: Provides optimized performance and overload protection using total system communication between tool, battery and charger •Best-in-class construction: Offers long-lasting performance and durability •Fuel gauge onboard: Displays remaining runtime for less downtime on the job •All-weather performance: Delivers fade-free power in extreme jobsite conditions •Powers all Milwaukee M12™ cordless power tools  
Part No. 48-11-2440.



### M12™ AC/DC WALL & VEHICLE CHARGER

•Dual-function design: AC wall charger and DC vehicle charger in a single unit •Single-unit simplicity: Quickly charges all M12™ REDLITHIUM and M12™ Lithium-Ion batteries in 40-80 minutes •Charge management: Charger communicates with the battery pack to ensure a full charge and battery protection •Onboard indicator light: Provides the status of the battery  
Part No. 2510-20.



### M12™ LITHIUM-ION BATTERY CHARGER

•Single unit simplicity: Charges M12™ RED LITHIUM™ and M12™ Lithium-Ion batteries •Charge management: Charger communicates with the battery pack to ensure a full charge and battery protection •Onboard indicator light: Provides the status of the battery •Pass-through plug: Conserves valuable outlet space  
Part No. 48-59-2401.



### M12™ & M18™ MULTI-VOLTAGE CHARGER

•Single unit simplicity: Quickly charges all M12™ and M18™ Battery Packs •Reduces time to manage charge cycles by sequentially charging the battery packs •Charge management: Charger communicates with the battery pack to ensure a full charge and battery protection  
Part No. 48-59-1812.



## M4 Cordless Power Tools

### M4™ 1/4" HEX SCREWDRIVER KIT

Featuring 44 in-lbs of peak torque and a 21-position clutch with auto shut-off, the new screwdriver offers improved torque control during repetitive applications. Two speeds, 200 and 600 RPM, offer further user control for precision work. At only 244 millimeters in length and under one pound, the M4™ Screwdriver is easy to use with one hand, featuring 1/2" quick-change chuck for one-handed bit changes. Drilling more than 200 holes per charge, the M4™ Screwdriver is the first tool to feature Milwaukee's RED LITHIUM™ 2.0 battery on the new M4™ platform, offering up to 50% more runtime. Milwaukee remains committed to offering innovative solutions in power, productivity, and portability.  
Set Includes: (1) 1/4" Hex Screwdriver, (2) M4™ 2.0 Battery, (1) M4™ Charger  
Part No. 2101-22.



## Cordless Tool Accessories

### LED BULB UPGRADE

•Replaces M12, M18, V28 and 9.6V - 28V incandescent bulbs - LED replacement for most work lights •3X runtime - increased efficiency for all work lights •50,000 hr LED - lasts over 250X longer than 18V incandescent bulb •Impact resistant - solid state light element does not fail when dropped •Compatible with Milwaukee M12, M18, V28 and most other major power tool work lights  
Part No. 49-81-0090.



Part No. 49-81-0040, Pack of 2, V28 work light bulbs

### CONTRACTOR BAG

Soft side contractor bag made of tough water resistant 600 denier material. Provides extra storage for job site tools and accessories. Shoulder strap or dual handle straps for easy carrying. Durable zipper closure. 20 1/2" L x 9" W by 8" H.  
Part No. 48-55-3500.



### 2.4V Ni-Cd STICK STYLE BATTERY

The hard-working Milwaukee 48-11-0100 2.4-Volt, 1.3-Amp Hour Battery powers Milwaukee's cordless screwdrivers and caulking guns. A lot of power in a compact design.  
Part No. 48-11-0100.



### 14.4V Ni-Cd BATTERY

•2.4 amp-hour capacity: Delivers longer runtime •No memory effect: Full capacity of 14.4-Volt NiCd battery is always available •Reversible battery pack: Allows users to work in tight spaces •Versatility: Powers all 14.4-volt Milwaukee cordless power tools  
Part No. 48-11-1024.



### 18V Ni-Cd BATTERY

•Highest quality cells: Deliver ultimate performance and long battery life •No memory effect: Full capacity of 18V NiCd battery is always available •Fast changeouts: Release latches are easy to operate •Versatility: Powers all 18V NiCd and V18™ Milwaukee cordless power tools  
Part No. 48-11-2230.



### 4V LITHIUM-ION CHARGER

•Charges 4V Li-Ion Battery in 30 minutes or less •Easy to load battery design •Slim profile conserves bench top space •Optional post mount attachment points on bottom of charger  
Part No. 48-59-0490.



### ONE HOUR Ni-Cd AC CHARGER

The One Hour NiCd Power Plus 120 volt AC charger will recharge 12V, 14.4V and 18V Power Plus Batteries. Recharges both Nickel Cadmium and Nickel Metal Hydride batteries. Charges batteries in one hour.  
Part No. 48-59-0255.

