



Crouse-Hinds By EATON CG150 1250

Crouse-Hinds By EATON Electrogalvanized Steel Straight Cord And Cable Connector, 1-1/2 IN MNPT, 1.15 - 1.25 IN Cable

MPN: CG150 1250

TRC Part#: CRHICG1501250

UPC: 78456400117

| Min Order Quantity: 1

| Quantity Interval: 1

DESCRIPTIONS

Straight Cord And Cable Connector, Size: 1-1/2 IN MNPT, Conductor Range: 1.15 - 1.25 IN, Material: Steel, Finish: Electrogalvanized, Color: Red, NEMA Rating: NEMA 4, Connection: Threaded

SPECIFICATIONS

Item Name: Straight Cord And Cable Connector

Size: 1-1/2 IN MNPT

Conductor Range: 1.15 - 1.25 IN

Material: Steel

Finish: Electrogalvanized

Color: Red

NEMA Rating: NEMA 4

Connection: Threaded

FEATURES

Neoprene bushings are color coded by cable diameter for quick and easy identification of proper cord grip

Rugged construction protects cord from damage

Compact design permits close spacing of fittings on panel applications

Tightening one nut creates watertight seal

Available in straight, 45 and 90 DEG entrance configurations

Nut are electrogalvanized steel and bushing are neoprene/natural

10 per pack

Standards: UL standard: 514B, CSA standard: C22.2 number 18

Applications: For use with portable cords, including S, SO, STO, ST, SJ, SJT, SJTO and SVO

DOCUMENTS

[Brochure](#)

