



On Line Catalog



BURNDY Catalog Number	KS17
UPC Number	7818100115088
Description	SERVIT 8STR - 6SOL
Status	Active
Web Use	
BURNDY Product Line	
	Dimensional
Width (in)	0.45
Size (Hex) or Size (Bolt)	7/16
Cross Flats	0.63
Size (Hex) or Size (Bolt) - in	0.438
B Length (in)	.58
B Length (Fraction)	29/50
	General
Product Description	Copper Split Bolt, Cu: 8 AWG (Str)-6 AWG (Sol) (Run & Tap),Length:1.14
	Conductor(s)
Copper Tap Range	14 AWG-6 AWG
CopperWeld Solid Run Size (Range)	6 AWG
Copper Stranded Run (Range)	8 AWG-6 AWG
CopperWeld Stranded Tap Size (Range)	9-1/2 D-3#12
Copper Solid Tap (Range)	14 AWG-6 AWG
CopperWeld Solid Tap Size (Range)	6 AWG
Copper Solid Run Size (Range)	8 AWG-6 AWG
CopperWeld Stranded Run Size (Range)	9-1/2D -3#12
	Physical
Installation Torque	165
Type of Plating	Unplated
Connector Type	Split Bolt
Plated (Yes or No)	N
Product Material	Copper
	Approvals / Certifications
Rated for Direct Burial	Y
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Industry Standards	RUS
Documentation	

For further technical assistance, please contact us

