



On Line Catalog



BURNDY Catalog Number	KSA6
UPC Number	7818100153533
Description	TRITAP SERVIT 6STR-10SOL
Status	Active

Web Use
BURNDY Product Line

	Dimensional
Width (in)	0.56
Height (in)	0.64
Size (Hex) or Size (Bolt)	9/16
Cross Flats	0.75
Size (Hex) or Size (Bolt) - in	0.56
B Length (in)	1.06
Bolt Diameter (in)	0.56
Min Tap Size with Max Run Size	#6 Str. (.184) - #10 Sol. (.102)
Max Tap size with Max Run Size	#6 Str. (.184) - #6 Str. (.184)
Min Tap Size with Min Run Size	#10 Sol. (.102) - #10 Sol. (.102)
B Length (Fraction)	1

	General
Product Description	Aluminum Split Bolt, (Run,Tap):: Al-Al: 6 AWG (Str), 6 AWG (Str) , Al-Cu: 10 AWG (Str), 10 AWG (Sol) , Cu-Cu: 6 AWG (Str), 10 AWG (Sol), Tin Plated

	Conductor(s)
Aluminum Run Size (Range)	8 AWG-6 AWG
Copper Tap Range	10 AWG-6 AWG
Copper Stranded Run (Range)	10 AWG-6 AWG
Copper Solid Tap (Range)	10 AWG-6 AWG
Aluminum Tap Size (Range)	8 AWG-6 AWG

	Physical
Installation Torque	165
Type of Plating	Tin
Plated (Yes or No)	Y
Product Material	Aluminum

	Approvals / Certifications
Rated for Direct Burial	N
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Industry Standards	UL468A-468B
Documentation	

For further technical assistance, please contact us

BURNDY LLC - USA

BURNDY Technical Services

Hours: 8:00 AM - 5:00 PM
Monday - Friday

