



Product Number: 10129

Order Abbreviation: 40A15/CL/APPL/BL 120V

General Description: Incandescent A15 Bulb Shape Appliance Clear Medium Aluminum Base 40Watt 120Volt Blister 12Bulbs Per Case 1Bulb Per Package

*** Full Case Required**

Product Information

Abbrev. With Packaging Info.	40A15CLAPPLBL 120V 12/CS 1/SKU
Approx. Lumens	430
Average Rated Life (hr)	1000
Base	Medium
Bulb	A15
Class	C (gas)
Color Rendering Index (CRI)	100
Color Temperature/CCT (K)	2850
Diameter (in)	1.875
Diameter (mm)	47.62
Filament	C-9
Lamp Finish	Clear
Light Center Length - LCL (in)	2.375
Light Center Length - LCL (mm)	60
Maximum Overall Length - MOL (in)	3.500
Maximum Overall Length - MOL (mm)	88.9
Nominal Voltage (V)	120.00
Nominal Wattage (W)	40.00



Footnotes

- Rated for oven use.