



BURNDY Catalog Number
UPC Number
Description
Status

YA3C2N
 7818100193755
 CULUG- 3 STR-2 LONG-NEMA
 Active

Web Use
 BURNDY Product Line

Tongue Angle
 Length (in)
 Tongue Type
 Barrell Style
 Bolt Hole Size (in)
 Barrel Type
 Thickness
 B Length (in)
 Pad Width (in)
 E - in
 Strip Length

Dimensional

Straight
 4.62
 Standard
 Chamfered
 0.52
 Long
 0.12
 1.25
 0.83
 1.75
 1-5/16

Number of Holes

General

2
 Copper Compression Lug, 2 Hole
 w/o Inspection Window, 3
 AWG(Str)/2 AWG(Sol), 1/2" Stud,
 1-3/4" Stud Hole Spacing, Long
 Barrel, Tin Plated

Product Description

Conductor(s)

Flex (Class G) Size - Range
 Flex (Class H) Size - Range
 Flex (Class I) Size - Range
 Copper Solid Size (Range)
 DLO Size (Range)
 Copper Stranded (Range)

N/A
 N/A
 N/A
 2 AWG
 N/A
 3 AWG

Type of Plating
 Bolt Hole Size
 Color Code
 Plated (Yes or No)
 Index Number
 Product Material

Physical

Tin - Electro Plated
 1/2
 White
 Y
 9
 Copper

Approvals / Certifications

UL Listed
 CSA Certified
 ROHS Compatible
 UL Recognized
 CULUS
 Industry Standards

Y
 Y
 Compliant
 N
 N
 UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175