



On Line Catalog



BURNDY Catalog Number

KSU34

UPC Number

7818100371022

Description

SERVIT UNIV 400-500

Status

Active

Web Use

BURNDY Product Line

Dimensional

Width (in)

1.47

Cross Flats

2.00

General

Product Description

Tin-plated, high strength copper alloy SERVITâ. ϕ with spacer. Spacer separates dissimilar conductors and provides long contact length that prevents high pressure point contacts between run and tap conductors.

Conductor(s)

Copper Tap Range

2 AWG-500 kcmil

CopperWeld Solid Run Size (Range)

N/A

Copper Stranded Run (Range)

400 kcmil-500 kcmil

CopperWeld Stranded Tap Size (Range)

N/A

Copper Solid Tap (Range)

N/A

CopperWeld Solid Tap Size (Range)

N/A

Copper Solid Run Size (Range)

N/A

CopperWeld Stranded Run Size (Range)

N/A

Physical

Installation Torque

825

Type of Plating

Tin - Electro Plated

Connector Type

Split Bolt

Plated (Yes or No)

Y

Product Material

Copper

Approvals / Certifications

UL Listed

Y

CSA Certified

Y

ROHS Compatible

Exempt

UL Recognized

N

CULUS

N

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175