



On Line Catalog



BURNDY Catalog Number
UPC Number
Description
Status

BIPC3504/0
7818101287322
350-4/0AWG INSL PRC CONN
Active

Web Use
BURNDY Product Line

	Dimensional
Width (in)	2.50
Length (in)	1.59
Bolt Size (in)	0.38
Height (in)	3.00
	Electrical
Max Voltage Rating	300
	General
Product Description	Insulation Piercing Connector, 4/0 AWG-350 kcmil (Run), 10-4/0 AWG (Tap), 300 V
	Conductor(s)
Aluminum Run Size (Range)	4/0 AWG-350 kcmil
Copper Tap Range	10 AWG-4/0 AWG
Copper Stranded Run (Range)	4/0 AWG-350 kcmil
Aluminum Tap Size (Range)	8 AWG-4/0 AWG
	Physical
Installation Torque	375
Type of Plating	Unplated
Plated (Yes or No)	N
	Approvals / Certifications
UL Listed	Y
CSA Certified	Y
Rated for Direct Burial	N
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Industry Standards	UL468A-468B
Documentation	

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175