



On Line Catalog



BURNDY Catalog Number

BIBD3504

UPC Number

7818101334533

Description

350-10, 2-SIDE, UNI-TAP, 4.04 IN L

Status

Active

Web Use

BURNDY Product Line

Dimensional

Width (in) 3.00
 Hex Size (Key) 5/16
 Length (in) 4.04
 Height (in) 2.50

Electrical

Min Voltage Rating 600

General

Number of Ports 4
 Number of Screws 4

Product Description

Aluminum Multiple Tap
 Connector, Clear Insulated, 4 Port,
 2 Sided Entry, 10 AWG-350 kcmil,
 Al/Cu Rated

Conductor(s)

Aluminum Size (Range) 8 AWG-350 kcmil
 Copper Solid Size (Range) N/A
 Copper Stranded (Range) 10 AWG-350 kcmil

Physical

Type of Hardware Aluminum
 Type of Plating Unplated
 Insulation Type Plastisol
 Plated (Yes or No) N
 Product Material Aluminum

Approvals / Certifications

Rated for Direct Burial N
 UL Listed Y
 CSA Certified Y
 ROHS Compatible Compliant
 UL Recognized N
 CULUS N
 Industry Standards UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175