



BURNDY Catalog Number

BIBS3504

UPC Number

7818101334911

Description

350-10, 1-SIDE, UNI-TAP, 4.04 IN L

Status

Active

Web Use

BURNDY Product Line

Dimensional

Width (in) 2.32
Hex Size (Key) 5/16
Length (in) 4.04
Height (in) 2.50

Electrical

Min Voltage Rating 600

General

Number of Ports 4
Number of Screws 10
Product Description Aluminum Multiple Tap
Connector, Clear Insulated, 4 Port,
1 Sided Entry, 10 AWG-350 kcmil,
Al/Cu Rated

Conductor(s)

Aluminum Size (Range) 8 AWG-350 kcmil
Copper Solid Size (Range) N/A
Copper Stranded (Range) 10 AWG-350 kcmil

Physical

Type of Hardware Aluminum
Type of Plating Unplated
Insulation Type Plastisol
Plated (Yes or No) N
Product Material Aluminum

Approvals / Certifications

Rated for Direct Burial N
UL Listed Y
CSA Certified Y
ROHS Compatible Compliant
UL Recognized N
CULUS N
Industry Standards UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175