



On Line Catalog



BURNDY Catalog Number

BITO2/0

UPC Number

7818101335522

Description

2/0-14, 2 SIDE, UNITAP

Status

Active

Web Use

BURNDY Product Line

Dimensional

Width (in) 1.56
 Hex Size (Key) 3/16
 Length (in) 1.52
 Height (in) 1.38

Electrical

Min Voltage Rating 600

General

Number of Ports 2
 Number of Screws 2
 Product Description Aluminum Multiple Tap Connector, Clear Insulated, 2 Port, 2 Sided Entry, 14-2/0 AWG, Al/Cu Rated, 1.52 L, 1.38 H

Conductor(s)

Aluminum Size (Range) 8 AWG-2/0 AWG
 Copper Solid Size (Range) N/A
 Copper Stranded (Range) 14 AWG-2/0 AWG

Physical

Type of Hardware Aluminum
 Type of Plating Unplated
 Insulation Type Plastisol
 Plated (Yes or No) N
 Product Material Aluminum

Approvals / Certifications

Rated for Direct Burial N
 UL Listed Y
 CSA Certified Y
 ROHS Compatible Compliant
 UL Recognized N
 CULUS N
 Industry Standards UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175