



On Line Catalog



BURNDY Catalog Number	KSA350
UPC Number	7818101835266
Description	TRITAP SERVIT 350-4STR
Status	Active

Web Use
BURNDY Product Line

	Dimensional
Width (in)	1.50
Height (in)	1.50
Size (Hex) or Size (Bolt)	1-3/8
Cross Flats	1.69
Size (Hex) or Size (Bolt) - in	1.38
B Length (in)	2.18
Bolt Diameter (in)	1.50
Min Tap Size with Max Run Size	350 kcmil (.681) - #4 Str. (.232)
Max Tap size with Max Run Size	350 kcmil (.681) - 350 kcmil (.681)
Min Tap Size with Min Run Size	#1/0 Str. Compact (.336) - #4 Str. (.232)
B Length (Fraction)	2-1/6

	General
Product Description	Aluminum Split Bolt, (Run,Tap):: Al-Al: 350 kcmil, 350 kcmil , Al-Cu: 1/0 AWG (Str), 4 AWG (Str) , Cu-Cu: 350 kcmil, 4 AWG (Str), Tin Plated

	Conductor(s)
Aluminum Run Size (Range)	1/0 AWG-350 kcmil
Copper Tap Range	4 AWG-350 kcmil
Copper Stranded Run (Range)	1/0 -350 kcmil
Copper Solid Tap (Range)	8 AWG-2 AWG
Aluminum Tap Size (Range)	4 AWG-350 kcmil

	Physical
Installation Torque	650
Type of Plating	Tin
Plated (Yes or No)	Y
Product Material	Aluminum

	Approvals / Certifications
Rated for Direct Burial	N
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Compliant
UL Recognized	N
CULUS	N
Industry Standards	UL468A-468B
Documentation	

For further technical assistance, please contact us

