



**Country Of Origin:** Please Contact Customer Service.



## R6RM

### 6" Integrated LED Recessed Remodel Downlight

- Specification grade 6" housing available in six (6) wattage/lumen packages
- Requires minimum 3" clearance around fixture from insulation material. Thermal protection provided in case of improper insulation use.
- Light engine consists of a single, high output multi-chip LED array enabling precise optical control
- Excellent fixture-to-fixture color consistency with a 3-step MacAdam Ellipse tolerance
- Quick-connect LED light engine enables easy installation and removal
- LED Drivers are fully accessible from below the ceiling and can be easily removed
- Available in: 2700K, 3000K, 3500K, and 4000K color temperatures with a CRI of 80 min., 83 typical. High CRI available.
- All R6SA downlights are available for non-dimming and dimming applications
- cCSAus Certified to UL Standards. Suitable for damp locations
- Assembled in the USA

### Technical Information

**Product Features**

**Aperture Size:** 6 in

**Color Rendering Index:** 80-89, 90-100

**Correlated Color Temperature:** 2700K, 3000K, 3500K, 4000K

**Listings:** Energy Star, Damp Location, Wet Location

**Lumen Output:** 501-1000, 1001-1500, 1501-2000, 2001-3000, 3001-4000

**Mounting:** Recessed

**Product Shape:** Round

**Product Type:** Downlight, Housing, Remodel