


[On Line Catalog](#)


BURNDY Catalog Number
UPC Number

BIBD2/02

7818102239322

Description

2/0-14 TWO SIDED UNITAP, 1.52

Status

IN L

Active

Web Use

BURNDY Product Line

Dimensional

Width (in)

1.56

Hex Size (Key)

3/16

Length (in)

1.52

Height (in)

1.38

Electrical

Min Voltage Rating

600

General

Number of Ports

2

Number of Screws

2

Product Description

Aluminum Multiple Tap
Connector, Clear Insulated, 2 Port,
2 Sided Entry, 14-2/0 AWG, Al/Cu
Rated**Conductor(s)**

Aluminum Size (Range)

8 AWG-2/0 AWG

Copper Solid Size (Range)

N/A

Copper Stranded (Range)

14 AWG-2/0 Str

Physical

Type of Hardware

Aluminum

Type of Plating

Unplated

Insulation Type

Plastisol

Plated (Yes or No)

N

Product Material

Aluminum

Approvals / Certifications

Rated for Direct Burial

N

UL Listed

Y

CSA Certified

Y

ROHS Compatible

Compliant

UL Recognized

N

CULUS

N

Industry Standards

UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA47 East Industrial Park Drive
Manchester NH 03109**BURNDY Technical Services**47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM

Monday - Friday

Phone: 800-346-4175