



BURNDY Catalog Number
UPC Number
Description
Status

GAR644C
7818102380044
8-4CU 3/8IPS
Active

Web Use
BURNDY Product Line

Dimensional

Width (in) 2.06
Length (in) 1.31
Height (in) 2.88
Size (Hex) or Size (Bolt) 3/8
Size (Hex) or Size (Bolt) - in 0.38
B Length (in) 1.50
Width (Fraction) 2-1/8
Height (Fraction) (in) 2-7/8

General

Mechanical Grounding Connector,
Cable to Rod or Pipe, 8 AWG
(Sol)- 4 AWG (Str), 3/8" Pipe,
5/8"-3/4" Rod, #5-#6 Rebar,
Bright Dipped

Product Description

Other

269

Approvals / Certifications

UL Listed Y
CSA Certified Y
ROHS Compatible Exempt
UL Recognized N
CULUS N
Industry Standards UL467
Rated for Direct Burial Y

Conductor(s)

Copper Tube Size (SCH40) - Range 3/8 IPS IPS
Rod Size (Range) 5/8 in-3/4 in
Copper Solid Size (Range) 8 AWG-3 AWG
Copper Stranded (Range) 9 AWG-4 AWG
Rebar Size (Range) 5 -6

Physical

Type of Hardware DURIUM® Silicon Bronze
Installation Torque 240
Type of Plating Bright Dipped
Plated (Yes or No) N
Product Material Copper Alloy

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175