



In-Wall Controls: Electronic In-Wall Timers

ST700W | Heavy-Duty 7-Day Programmable Timer



ST700W

HEAVY-DUTY 7-DAY PROGRAMMABLE TIMER

The Ascend® Standard In-Wall Timer is a 7-Day Programmable Timer featuring a sleek, modern design. The timer can be configured in minutes using a large backlit LCD display and includes pre-programmed templates for easy use. The Ascend Standard features Astronomic dusk-to-dawn settings and automatic Daylight Saving Time adjustments. Neutral required.

Next Generation Timers with sleek, modern design and intuitive programming. Neutral Required. Communication Enabled and Non-communication units available.



Features & Applications

Features

Applications

- Sleek, Modern Design
- Automatic Astronomic
- Automatic Daylight Saving Time (DST) Adjustment
- Intuitive Setup
- Three pre-programmed schedule templates for convenience
- Fully customized scheduling for flexibility
- Program up to 42 unique events
- Large LCD Display
- Non-replaceable battery backup keeps time and date information in the event of a power loss
- Schedules and other settings are kept indefinitely in non-volatile memory
- Garage
- Driveway
- Common Area
- Hallway
- Patio
- Front Door
- Outdoor Path
- Coach Lights

Specifications

Color White	Incandescent Load Ratings (Multi-Gang) 8 A, 120 VAC, 50/60 Hz	Operating Temperature Min (°C) -20
Operation Mode 24-hours, 7-day	Electronic Ballast 5 A, 120 VAC, 50/60 Hz	Operating Temperature Min (F) -4
Operation Features Astronomic, Daylight Saving Time	Inductive 15 A, 120 VAC, 50/60 Hz	Product Width (in) 1 3/4
Application Compatibilities CFL, Fluorescent, Incandescent, LED	Motor 1 HP, 120 VAC, 50/60 Hz	Product Height (in) 2 3/4
Wall Plate Configurations Single-Gang	Operating Temperature Max (°C) 50	Product Height (mm) 69.9
Wiring Configurations	Operating Temperature Max (F)	Product Width (mm) 44.4

3-Way, Single

122

Has Wi-Fi

No

Minimum ON/OFF Times

1 min

Maximum ON/OFF
Operations

44

Backup Type

Battery

Battery Type

CR2032

Product Depth (in)

1 1/3

Product Depth (mm)

33.9

Other Certifications

Title 20

Warranty

3-Year limited

For California residents, click [here](#) for Proposition 65 Warning.

[Videos](#)