



S8930

40W/LED/HID/WP/5K/E39/100-277V
40 watt LED Hi-lumen, omni-directional lamp for commercial
fixture applications; 5000K; Mogul base; 100-277 volts

Features

- High Lumen Omni-directional LED for use in wall pack, canopy, shoe box, or cobra head fixture
- Replaces HID, CFL, and Incandescent
- Ballast by-pass - Direct wire only 100V - 277V
- UL approved for totally enclosed fixtures
- Horizontal operation
- Emits no UV light / Contains no mercury (Hg)
- 5 year limited warranty
- DLC Listed
- cULus listed



S8930

Minimum Compartment Size		
Length	Width	Depth
8 inch	8 inch	11 inch

Optional accessory: In-line surge protector [80-929](#)

Item Number	Product Line	UPC	Input Voltage	Watts	Operating Frequency	HID Equivalent	Base
S8930	Hi-Pro	045923089305	100 - 277	40	50/60Hz	175W	Mogul

ANSI Base	Lamp Code	Dimmable/Non-Dimmable	Finish	MOL In Inches	MOD In Inches	Initial Lumens	Average Rated Hours
E39	40W/LED/HID/WP/5K/E39/100-277V	Non-Dimmable	White	8-1/2"	3-1/8"	6000	50000

Kelvin Temp	Color	CRI	Beam Spread Deg	Operating Temperature	Pack	Package Type	CEC Status
5000	Natural Light	80+	180	-40C (-40F) to a maximum of +60C (+140F)	12	Box	Lawful for sale in California
DLC ID:		RoHS Compliant		UL or ETL Listed	UL Classification		Warranty

PL2YDXWVA1LX
[DLC Search](#)

Yes

Yes

cULus - Damp Location Rated

[5 Year Limited](#)



National Toll-Free:
800.43.SATCO
(800.437.2826)
www.satco.com

Distribution Centers:
New York, Florida, Texas,
Washington, California,
Puerto Rico

Corporate Offices:
110 Heartland Blvd.,
Brentwood, NY 11717
800.437.2826 631.243.2022
Fax 631.243.2027



©2012, Satco Products, Inc. Not responsible for typographical errors. 06/12 S1051