



BURNDY Catalog Number
UPC Number
Description
Status

KLU35
 7818103513766
 14-6 CU LUG BLT
 Active

Web Use
 BURNDY Product Line

Dimensional

Screw Size	1/4
Length (in)	1.24
Size (Hex) or Size (Bolt)	1/4
Stud Size (in)	#10
Thickness	0.07
Size (Hex) or Size (Bolt) - in	0.25
B Length (in)	0.33
Pad Width (in)	0.39
N (in)	0.22
Hole Size (in)	0.20
Strip Length	5/8
B Length (Fraction)	1/3

General

Product Description	Copper Terminal, Offset Tongue, 1 Hole, 14 AWG (Sol)-6 AWG (Str), #10 Stud, 1 Screw
---------------------	---

Conductor(s)

Copper Solid Size (Range)	14 AWG-6 AWG
Copper Stranded (Range)	14 AWG-6 AWG

Physical

Screw Type	Slot
Installation Torque	45
Type of Plating	Unplated
Connector Type	Terminal
Plated (Yes or No)	N
Product Material	Copper

Approvals / Certifications

Rated for Direct Burial	N
UL Listed	N
CSA Certified	N
ROHS Compatible	Compliant
UL Recognized	N
CULUS	Y
Industry Standards	UL467

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175