



**BURNDY Catalog Number**  
**UPC Number**  
**Description**  
**Status**

KLU70  
 7818103513833  
 8-2 CU LUG BLT  
 Active

**Web Use**  
 BURNDY Product Line

#### Dimensional

|                                |       |
|--------------------------------|-------|
| Screw Size                     | 5/16  |
| Length (in)                    | 1.56  |
| Size (Hex) or Size (Bolt)      | 5/16  |
| Stud Size (in)                 | 1/4   |
| Thickness                      | 0.08  |
| Size (Hex) or Size (Bolt) - in | 0.31  |
| B Length (in)                  | 0.46  |
| Pad Width (in)                 | 0.47  |
| N (in)                         | 0.25  |
| Hole Size (in)                 | 0.26  |
| Strip Length                   | 3/4   |
| B Length (Fraction)            | 23/50 |

#### General

|                     |                                                                                     |
|---------------------|-------------------------------------------------------------------------------------|
| Product Description | Copper Terminal, Offset Tongue, 1 Hole, 8 AWG (Sol)-2 AWG (Str), 1/4" Stud, 1 Screw |
|---------------------|-------------------------------------------------------------------------------------|

#### Conductor(s)

|                           |             |
|---------------------------|-------------|
| Copper Solid Size (Range) | 8 AWG-2 AWG |
| Copper Stranded (Range)   | 8 AWG-2 AWG |

#### Physical

|                     |          |
|---------------------|----------|
| Screw Type          | Slot     |
| Installation Torque | 50       |
| Type of Plating     | Unplated |
| Connector Type      | Terminal |
| Plated (Yes or No)  | N        |
| Product Material    | Copper   |

#### Approvals / Certifications

|                         |           |
|-------------------------|-----------|
| Rated for Direct Burial | N         |
| UL Listed               | N         |
| CSA Certified           | N         |
| ROHS Compatible         | Compliant |
| UL Recognized           | N         |
| CULUS                   | Y         |
| Industry Standards      | UL467     |

#### Documentation

**For further technical assistance, please contact us**

#### BURNDY LLC - USA

47 East Industrial Park Drive  
 Manchester NH 03109

#### BURNDY Technical Services

47 East Industrial Park Drive  
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM  
 Monday - Friday  
 Phone: 800-346-4175