



7543493S-782: Small LED Ceiling Flush Mount



Dimensions:

Diameter: 11 1/2"
Height: 4"
Weight: 2.9 lbs.

Wire: 6 1/2" (color/Black/White)
Mounting Proc.: Cap Nuts
Connection: Mounted To Box
Bulb Type: Modules
Bulb Base: Integrated
Volts: 120
Watts: 14
Watts Consumed: 14
Watts Rated: 14
Hours Rated: 50000
Lumens: 1000
Bulb Temp: 30000 °K
CRI: 90

Collection: Nash

LED Flush Mount Fixture in Chrome Finish with Satin Etched Glass Shade

UPC #:785652064739

Finish: Heirloom Bronze (782)

Features:

- ENERGY STAR® Qualified
- Advanced LED technology that warms in color when dimmed (3000K - 2200K).
- Meets Title 24 energy efficiency standards
- Integrated LED fixtures that meet the high efficacy LED standards set forth in Title 24 and are listed in the California Energy Commission Appliance database.
- Sleek architectural look with exclusive 'twist-lock' design makes installation and relamping easy with no exposed screws

Material List:

1 Body - Steel - Heirloom Bronze

Safety Listing:

Safety Listed for Damp Locations

Instruction Sheets:

French (F-003)
Trilingual (English, Spanish, and French) (990C7543_-NSH)

Shade / Glass / Diffuser Details:

Part	Material	Finish	Quantity	Item Number	Length	Width	Height	Diameter	Fitter Diameter	Shade Top Length	Shade Top Width	Shade Top Diameter
Diffuser	Glass	Satin Etched	1	G510037-619			3 1/4	9				

Shipping Information:

Package Type	Product #	Quantity	UPC	Length	Width	Height	Cube	Weight	Fr. Class	UPS Ship
Individual	7543493S-782	1	785652064739	13	12.75	6.5	0.623	4	125	Yes
NJ Pallet		114		48	40	73	81.111	456		No
NV Pallet		114		48	40	73	81.111	456		No