



BURNDY Catalog Number
UPC Number
Description
Status

KA30U
 7818103702233
 6STR-300 DUAL RATED
 Active

Web Use
 BURNDY Product Line

Dimensional

Width (in)	1.00
Length (in)	2.00
Bolt Hole Size (in)	0.31
Thickness	0.25
D - in	0.94
Pad Width (in)	1.02
N (in)	0.45

General

Number of Conductors	1
Number of Holes	1
Product Description	Aluminum Universal Terminal, 1 Hole, 6 AWG (Str)-300 kcmil, 5/16" Stud, 1 Screw, Al/Cu Rated, Tin Plated

Conductor(s)

Aluminum Size (Range)	6 STR- 300 kcmil
Copper Solid Size (Range)	4 AWG-4/0 AWG
Copper Stranded (Range)	6 AWG-300 kcmil

Physical

Installation Torque	275
Type of Plating	Tin
Connector Type	Terminal
Bolt Hole Size	5/16
Plated (Yes or No)	Y
Product Material	Aluminum

Approvals / Certifications

Rated for Direct Burial	N
UL Listed	Y
CSA Certified	Y
ROHS Compatible	Exempt
Industry Standards	UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
 Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
 Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
 Monday - Friday
 Phone: 800-346-4175