



BURNDY Catalog Number
UPC Number
Description
Status

K22A39U2
7818103703399
FOUR:1/0 STR-750 DUAL
Active

Web Use
BURNDY Product Line

Dimensional

Width (in) 3.06
Length (in) 4.91
Height (in) 3.02
Thickness 0.75
D - in 2.31
E - in 1.38
N (in) 0.38

General

Number of Conductors 4
Number of Holes 2
Product Description Aluminum Universal Terminal, 2 Hole, Four: 1/0 AWG (Str)-750 kcmil, 3/8" Stud, 1.38" Stud Hole Spacing, 4 Screws, Al/Cu Rated, Tin Plated

Conductor(s)

Aluminum Size (Range) 1/0 AWG-750 kcmil
Copper Solid Size (Range) N/A
Copper Stranded (Range) 1/0 -750 kcmil

Physical

Installation Torque 375
Type of Plating Tin
Connector Type Terminal
Plated (Yes or No) Y
Product Material Aluminum

Approvals / Certifications

Rated for Direct Burial N
UL Listed Y
CSA Certified Y
ROHS Compatible Non-Compliant
Industry Standards UL468A-468B

Documentation

For further technical assistance, please contact us

BURNDY LLC - USA

47 East Industrial Park Drive
Manchester NH 03109

BURNDY Technical Services

47 East Industrial Park Drive
Manchester NH 03109

Hours: 8:00 AM - 5:00 PM
Monday - Friday
Phone: 800-346-4175